



General Data

Code Radium	34317363
Désignation	XERADEX L40/120/SB-SX48/KF50/HV
EAN 10 (unité)	4008597173639
Unité de transport (pièces)	1
EAN 40 (carton)	4008597473630
Poids brut du carton en kg	1.375
Longueur box in m	0.35
Largeur du carton en m	0.33
Hauteur du carton en m	0.57
Product weight	475 g
Product status	● Actif

Electric Parameters

Lamp power	20.0 W
max. power without active cooling	20.0 W

Light Application Parameters

Type of UV radiation	UV-C
----------------------	------

Service Life

Life L70 without active cooling	2500 h
---------------------------------	--------

Specification

XERADEX UV special lamp

XERADEX L40/120/SB-SX48/KF50/HV

Radium

Diameter	40 mm
radiator length (glass)	120 mm

Specification

Lamp shape	Tube, single-ended
Base	Other

Notes on Operation

Generating ozone	Oui
Suitable for air disinfection	Oui
Suitable for water disinfection	Oui
Suitable Accessories	52312907

Notes

Xenon Excimer radiation source (UV-C), operation in air tight casing and with original ballast only. Ensure good air ventilation (ozone generating).

Please, refer to www.radium.de/recycling for notes on disposal of burned-out lamps as well as lamp breakage.

The field 'info about service life' contains the frame conditions according to standards based on which the specific service life has been determined. So, for example, "12B50, 50Hz" means that the mean service life (B50) has been determined with a 12h switching cycle at mains (frequency 50Hz), "3B50, HF" is based on a 3h switching cycle at electronic control gear (high frequency).

Notices explicatives générales

The technical design data in accordance with DIN and IEC. The producer does not take any responsibility for damage to persons or property in case of unsuitable operation or handling of the product. Operating data and dimensions are valid within the usual tolerances. Related lamp types (different bases, mains voltages) may be available on request. Sale and delivery are effected in accordance with the Radium Terms of Delivery and Payment valid on the day of conclusion of contract. Packing units offer economical advantages to the purchase and logistic department. Please match your quantity volume accordingly. For orders of a minimum quantity (clefts) with a lamp model the amount lower than the volume of each packaging unit, we will invoice 10 % additional charge per lamp type. Technical changes and terms of delivery are reserved. Manipulation of any kind to packaging or product is not permissible as this will violate Radium brand rights. Furthermore, technical properties of the product can change to its disadvantage or even destruction. Therefore, Radium cannot be responsible for consequential damages.

® = Registered trademark

Subject to change without notice. Errors and omissions excepted.

Consignes de sécurité

XERADEX lamps produce extremely intense UV radiation that is heavily absorbed by oxygen. Ozone is produced as a result. Adequate ventilation must therefore be provided during their operation. The lamps should be operated only in airtight enclosures. XERADEX lamps are operated at high voltage and may only be connected to original DBD control gear designed for this purpose. Never connect them to any other control gear. Lamps are operated at high voltage and may only be installed, exchanged and operated by qualified personnel.

All technical data without guarantee.